

TECHNICAL DATA SHEET EP1121 Clear

3/27/2020

N109 W13300 ELLSWORTH DRIVE GERMANTOWN, WI 53022 262-253-5900 FAX 262-253-5919

DESCRIPTION:

ResinLab® EP1121 Clear is a two part unfilled, epoxy encapsulant designed for medium to large sized castings. It cures completely at room temperature to a tough, flexible yet soft polymer. It has low viscosity to allow for good wicking and penetration into components and circuitry, and it also gives good air release. Thermal shock and cycling properties are also enhanced by its high elongation, giving it the ability to accommodate differences in the CTEs of varying substrates. It also has very good resistance to water, acids and bases, and most organic solvents.

EP1121 Clear was formulated to a 1A:1B volume mix ratio for use in side-by-side dispensing cartridges and meter, mix, and dispense (MMD) equipment. *EP1121 Clear* can also be used in a 1A:2B by volume ratio for certain applications.

At room temperature, *EP1121 Clear* at 1:1 will reach handle cure within 8 - 16 hours and full cure within 24 - 48 hours. Final cure properties can be achieved more quickly by the application of heat after product has gelled. Cure times and temperatures typical for most applications range from 1 hour at 65 °C to 15 minutes at 100 °C. Time to heat substrate must be taken into account with cooler temperatures extending the work time.

TYPICAL PROPERTIES:

All properties given are at 25 °C unless otherwise noted.

Property:	Value:1:1	Value:1:2	Test Method or Source:
Color	Clear	Clear	Visual
Mix Ratio	Part A to Part B	Part A to Part B	Calculated
By weight	1.14 to 1	1 to 1.75	
By volume	1 to 1	1 to 2	
Cure Schedule	24-48 hours @ 25 °C	96 hours @ 25 °C	
	1 hour @ 65 °C	1 hour @ 65 °C	
	15 minutes @ 100 °C	15 minutes @ 100 °C	
Viscosity – Part A	3,000 cps @1/s	3,000 cps @1/s	455300006291/Rheometer
Viscosity – Part B	3,000 cps @1/s	3,000 cps @1/s	parallel plate 25mm
Viscosity - Mixed	3,000 cps @1/s	3,000 cps @1/s	
Specific Gravity – Part A	1.11	1.11	Calculated
Specific Gravity – Part B	0.97	0.97	
Specific Gravity - Mixed	1.04	1.02	
Pot Life, defined as the time it takes	16 minutes	20 minutes	455300006291/Rheometer
for initial mixed viscosity to double			parallel plate 25mm@1/s
Gel Time	90 minutes/100cc sample	90 minutes/100cc sample	455300005339/Gardco Hot Pot Gel Timer
Glass Transition Temperature/Tg	36 °C	8 °C	453560822409 by DSC
Peak Exotherm	47 °C after 45 minutes for 40ml	48 °C after 45 minutes	455300005593 by Type K
- Can Exement	sample	for 40ml sample	thermocouple
Hardness	60 Shore D	40 Shore A	455300006287/ASTM D2240
Water Absorption	0.18% after 24 hours	N/A	457561824543/ASTM D570
Tensile Properties:			4535601224470/ASTM D638
Strength	1,000 psi	N/A	



TECHNICAL DATA SHEET EP1121 Clear

3/27/2020

N109 W13300 ELLSWORTH DRIVE GERMANTOWN, WI 53022 262-253-5900 FAX 262-253-5919

Elongation	70%		
Modulus	9,000 psi		
Lap Shear Strength			4535601224468/ASTM
0.010" bond line Al to Al	1,100 psi	N/A	D1002
Compressive Properties:			4535601224467/ASTM D695
Yield Strength	35,000 psi	N/A	
Compressive Strength	22,000 psi		
Modulus	410,000 psi		
Thermal Conductivity by Transient	0.20 W / (m.K)	N/A	45376013225604/Thermtest
Plane Heat Source (TPS)			TPS Hot Disk ISO 22007-2
Surface Resistivity	2.84 x 10 ¹⁴ ohm/sq (@ 35 %RH)	N/A	455300006612/ASTM D257
	3.92 x 10 ¹² ohm-cm (@ 22 °C)		
Volume Resistivity			
Dielectric Constant / Dissipation			455300006513/ASTM D150
Factor			
@ 100 Hz	3.3, 0.07	N/A	
@ 100 kHz	2.7, 0.03		
Coefficient of Thermal Expansion by	47 ppm/ °C below Tg	N/A	455300005340/ASTM E831
TMA	242 ppm/ °C above Tg		TMA, 5 °C/min
Operating Temperature Range	-40 to 150 °C**	-40 to 150 °C**	

^{**} Operating Temperature Range is based on average design requirements and is not intended as a guarantee of suitability for all applications operating at that temperature.

INSTRUCTIONS:

- Bring both components to room temperature prior to mixing.
- 2. Cartridge format: Mixer should be attached keeping the cartridge vertical and any air pocket purged this way. After the mixer contains material, the mixer tip can be dropped to dispense pre-bleed amount. Attach a new static mixer with each cartridge, then pre-bleed the first 3 inches of dispensed material or until a uniform color is obtained. Maintain adequate velocity during dispensing to ensure complete mixing.
- 3. Bulk format: weigh and mix parts A and B accurately and thoroughly, scraping sides of container often. Do not pour from mixing container, transfer to a new container as residual unmixed material may cause a tacky spot on the surface of the casting. Maintain adequate velocity during dispensing to ensure complete mixing.
- 4. Allow to cure undisturbed until product is fully gelled or tack-free to the touch.
- 5. Clean up uncured resin with suitable organic solvent such as MEK, acetone or other organic solvent.

^{***} This TDS contains values that have been updated. The values reported in this technical data sheet are typical values of the product, and are highly dependent on test conditions and methodology. We actively seek the most precise and accurate ways to measure and interpret performance of our products, and to update estimated values with measured values. The formula has not been revised or changed in any way. Although the values on paper have changed, you can expect the same performance of the product.



TECHNICAL DATA SHEET EP1121 Clear

3/27/2020

N109 W13300 ELLSWORTH DRIVE GERMANTOWN, WI 53022 262-253-5900 FAX 262-253-5919

SHELF LIFE AND STORAGE:

12 months at 25 °C Specialty packaging may be less.

Many epoxy resin systems are prone to crystallization as epoxy resin is a super-cooled fluid. This condition may give the product a gritty or grainy appearance (or hazy in clear products). Products in this state will not usually cure to normal and expected properties. In extreme cases it may appear solid and cured. Fluctuating temperatures (within 5 to 50 °C) aggravate this phenomenon. Heating the individual component to 50 to 60 °C while stirring can usually restore products to original state. Storage at 25 +/- 10 °C is optimum for most products.